



# Optivisor

INSTRUCTIONS • #002-710, #002-711, and 002-712



## Optivisor

The Optivisor helps users see work better. It features ground plastic lenses and an adjustable headband. Includes special kit for changing the position of each lens. We recommend starting out with an Optivisor #5 for first-time users.

**#3 Optivisor 1.75 Power • #002-710**

**#5 Optivisor 2.50 Power • #002-711**

**#7 Optivisor 2.75 Power • #002-712**



## Optivisor Lens Extension Kit PARTS LIST

- A. 6-32 x 1 1/4" Machine Screw
- B. Lens Plate
- C. Lens Spacers (Spacing may be set according to user's preferences.)
- D. Optivisor Housing
- E. 6-32 Hex Nut

## Optivisor Products

The following are additional products that can be purchased for your Optivisor. For pricing information, please call your sales representative today.

### Replacement Lenses

**#3 Lens Plate 1.75 Power • #002-965**

**#5 Lens Plate 2.50 Power • #002-966**

**#7 Lens Plate 2.75 Power • #002-967**

### Eye Loupe • #011-380

Triplet 10X, 18 mm lens.

High quality optics allow close inspection of tools and work.

Chrome finish, leather case.

### Optiloupe Kit • #022-119

Adds an extra 2.5 power to the Optivisor. Swings away when desired.

**GLENDO**  
CORPORATION

900 Overlander Road • Emporia, KS 66801 USA  
800-835-3519 • 620-343-1084 • Fax: 620-343-9640  
grs@grstools.com • www.grstools.com  
Last Updated: December 26, 2012

LIT-004-231